## **PROGRESS** LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:

## P500240-031 Winslett

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with this foyer light. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines. Sleek, candlestick-like light bases gather at the center of the open-cage design.

- Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines.
- Sleek, candlestick-like light bases gather at the center of the open-cage design.
- Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with this foyer light.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for transitional, rustic, farmhouse, and coastal settings.
- Measures 19-5/8-inch width by 25-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Hall & Foyer Finish: Matte Black (Painted) Construction: Steel Construction



Square: 19-5/8 in Height: 25 in Overall Ht. W/Chain: 99-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Four 60 W max. Candelabra Base	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	180" of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic sockets	
6 feet of 9 gauge chain supplied			

Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth