PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:

P500241-104 Clarion

Who says you have to sacrifice forms for function? This versatile pendant features a simple, clear glass shade that embraces minimalist modernity and functional task lighting. The glass shade rests at the end of a sleek polished nickel bar that attaches to the ceiling. Each light fixture has a swivel at its base that makes it perfect for installing on flat or angled ceilings.

- This versatile pendant features a simple, clear glass shade that embraces minimalist modernity and functional task lighting.
- The glass shade rests at the end of a sleek polished nickel bar that attaches to the ceiling.
- Each light fixture has a swivel at its base that makes it perfect for installing on flat or angled ceilings.
- Ideal for any foyer, dining room, or kitchen.
- Perfect for transitional, modern, farmhouse, coastal, contemporary, and luxury settings.
- Measures 9-inch width by 11-3/8-inch height.
- Uses one medium base bulb that is sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Polished Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear glass Cone shaped shade



Diameter: 9 in Height: 11-3/8 in Overall Ht. W/Stem: 67-1/2 in

Clear glass Cone shaped shade Width: 9 in Height: 10-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Prewired	Quantity: One 60 W max. Medium Base or	CULus Dry Location Listed
Mounting plate for outlet box	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
included	120 V	E26 base Porcelain socket	
One 6", four 12" lengths of stem included			

recessed outlet box: 5.125" W., 0.875" ht., 2.125" depth

Canopy covers a standard 4"