

Project:			
Fixture Type:			
Location:			

Contact:

P500243-009 Riley

Incorporate a sleek simplicity and natural beauty with this pendant. A stunning organza fabric shade redefines love at first sight. Beneath the shade peaks a stylishly simple brushed nickel frame with polished chrome straps that attaches to the ceiling by a thin metal bar.

- Incorporate a sleek simplicity and natural beauty with this pendant.
- · A stunning organza fabric shade redefines love at first sight.
- Beneath the shade peaks a stylishly simple brushed nickel frame with polished chrome accents that attaches to the ceiling by a thin metal bar.
- · Ideal for any foyer, kitchen, or dining room.
- · Perfect for new traditional or contemporary settings.
- · Measures 21-inch width by 11-inch height.
- Uses three candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Organza fabric drum shade



Diameter: 21 in Height: 11 in

Overall Ht. W/Chain: 77 in

Organza fabric drum shade

Width: 21 in Height: 7-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain	Prewired	Quantity: Three 60 W max. Candelabra	CULus Dry Location Listed
	15 feet of wire supplied	Base or LED equivalent	1-year Limited Warranty
1/8 IP mounting plate for outlet box included	120 V	E12 base Phenolic sockets	
Six links of 9 gauge chain supplied			
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 4.875" W., 0.75" ht., 4.875" depth			