

Project:			
Fixture Type:			
Location:			
Contact:			

P500274-009 Chadwick

Stick with simple geometric forms and clean crisp lines with this modern mini-pendant. A beautiful opal glass shade visually calms the sharp edges of the boxy frame in a masterful stroke of design excellence. The frame is coated in a classic brushed nickel finish that contrasts the light shade. The light fixture is just right for spaces in need of a subtle, feminine touch.

- A beautiful opal glass shade visually calms the sharp edges of the boxy frame in a masterful stroke of design excellence.
- The frame is coated in a classic brushed nickel finish that contrasts the light shade.
- The light fixtures is just right for spaces in need of a subtle, feminine touch.
- · Ideal for any foyer, hallway, dining room, or kitchen.
- $\boldsymbol{\cdot}$ Perfect for transitional, modern, and contemporary settings.
- · Measures 10-1/2-inch width by 14-3/4-inch height.
- Uses one medium base bulb that are sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Etched Opal glass Cylindrical Shade



Square: 10-1/2 in Height: 14-3/4 in

Overall Ht. W/Stem: 72 in

Etched Opal glass Cylindrical Shade

Width: 6-1/2 in Height: 7-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Dry Location Listed
Mounting plate for outlet box	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
included	120 V	E26 base Porcelain socket	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.812" ht., 4.5" depth			