

Project:
Fixture Type:
Location:



Diameter: 10 in Height: 11 in

Overall Ht. W/Chain: 76 in

P500281-031

Chambers

Contact:

Foster a down-home décor theme with this rustic mini-pendant. A simple egg-basket-inspired wire-frame shade grants the light fixture its signature country-look. Inside the open-cage shade is a vintage light bulb coated in a farmhouse-style black finish.

- A simple egg-basket-inspired wire-frame shade grants the light fixture its signature country-look.
- Inside the open-cage shade is a vintage light bulb coated in a farmhouse-style black finish.
- · Foster a down-home décor theme with this rustic mini-pendant.
- · Ideal for any foyer, kitchen, or dining room
- Can also be mounted as a ceiling light in a hallway or other close-to-ceiling application setting.
- · Perfect for urban industrial, rustic, farmhouse, or vintage electric settings.
- · Measures 10-inch width by 11-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- $\bullet \ \ \text{Progress Lighting products are designed for exceptional quality, reliability, and functionality. }$

Category: Pendants Finish: Matte Black (Painted) Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Dry Location Listed
Mounting plate for quitlet box	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
Mounting plate for outlet box included	120 V	E26 base Porcelain socket	
Six links of 9 gauge chain supplied			
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.812" ht., 5.12" depth			