

Project:
Fixture Type:
Location:



Diameter: 10 in Height: 11 in

Overall Ht. W/Chain: 76 in

## P500281-141

## **Chambers**

Contact:

Foster a down-home décor theme with this rustic mini-pendant. A simple egg-basket-inspired wire-frame shade grants the light fixture its signature country-look. Inside the open-cage shade is a vintage light bulb coated in a farmhouse-style galvanized finish.

- A simple egg-basket-inspired wire-frame shade grants the light fixture its signature country-look.
- Inside the open-cage shade is a vintage light bulb coated in a farmhouse-style galvanized finish.
- Foster a down-home décor theme with this rustic mini-pendant.
- · Ideal for any foyer, kitchen, or dining room
- Can also be mounted as a ceiling light in a hallway or other close-to-ceiling application setting.
- · Perfect for urban industrial, rustic, farmhouse, or vintage electric settings.
- · Measures 10-inch width by 11-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

**Finish:** Galvanized Finish (Painted) **Construction:** Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Dry Location Listed
	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
Mounting plate for outlet box	100.17	FOC have Developed	
included	120 V	E26 base Porcelain socket	
Six links of 9 gauge chain supplied			
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.812" ht., 5.12" depth			