



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P500282-141 Chambers

Foster a down-home décor theme with this rustic pendant. A simple egg-basket-inspired wire-frame shade grants the light fixture its signature country-look. Inside the open-cage shade is a vintage light bulb coated in a farmhouse-style galvanized finish.

- A simple egg-basket-inspired wire-frame shade grants the light fixture its signature country-look.
- Inside the open-cage shade is a vintage light bulb coated in a farmhouse-style galvanized finish.
- Foster a down-home décor theme with this rustic pendant.
- Ideal for any foyer, kitchen, or dining room
- Can also be mounted as a ceiling light in a hallway or other close-to-ceiling application setting.
- Perfect for urban industrial, rustic, farmhouse, or vintage electric settings.
- Measures 16-3/8-inch width by 10-7/8-inch height.
- Uses one medium base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Diameter: 16-3/8 in
 Height: 10-7/8 in
 Overall Ht. W/Chain: 76 in

Category: Pendants
Finish: Galvanized Finish (Painted)
Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity: One 60 W max. Medium Base or LED equivalent	CULus Dry Location Listed
Mounting plate for outlet box included	15 feet of wire supplied	E26 base Porcelain socket	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V		
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth			