

Project:			
Fixture Type:			
Location:			
Contact:			

P500283-031

Atwell

Extraordinary on the first impression, but always at peace with whatever setting it calls home, this pendant is a statement-making lighting design. The light fixture features an intricate blend of circular and a one-of-a-kind architectural designs that is both remarkable and enduring. A clear globe shade softens and contrasts with the frame's sharp corners.

- Extraordinary on the first impression, but always at peace with whatever setting it calls home, this pendant is a statement-making lighting design.
- A clear globe shade softens and contrasts with the frame's sharp corners.
- The light fixture features an intricate blend of circular and a one-of-a-kind architectural designs that is both remarkable and enduring.
- · Ideal for any foyer, kitchen, or dining room.
- Perfect for mid-century modern, modern, contemporary or luxury settings.
- Measures 8-1/4-inch width by 13.12-inch height.
- Uses one candelabra base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear glass Globe



Width: 8-1/4 in Height: 13-1/8 in Depth: 8-1/4 in

Overall Ht. W/Stem: 70 in

Clear glass Globe Width: 5-7/8 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Prewired	Quantity: One 60 W max. Candelabra Base	CULus Dry Location Listed
	10 feet of wire supplied	or LED equivalent	1-year Limited Warranty
Mounting plate for outlet box included	120 V	E12 base Porcelain socket	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 4.75" W.,			
0.81" ht., 4.75" depth			