

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500283-109

Atwell

Extraordinary on the first impression, but always at peace with whatever setting it calls home, this pendant is a statement-making lighting design. The light fixture features an intricate blend of circular and a one-of-a-kind architectural designs that is both remarkable and enduring. A clear globe shade softens and contrasts with the frame's sharp corners.

- Extraordinary on the first impression, but always at peace with whatever setting it calls home, this pendant is a statement-making lighting design.
- A clear globe shade softens and contrasts with the frame's sharp corners.
- The light fixture features an intricate blend of circular and a one-of-a-kind architectural designs that is both remarkable and enduring.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for mid-century modern, modern, contemporary or luxury settings.
- Measures 8-1/4-inch width by 13.12-inch height.
- Uses one candelabra base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Width: 8-1/4 in
Height: 13-1/8 in
Depth: 8-1/4 in
Overall Ht. W/Stem: 70 in

Clear glass Globe
Width: 5-7/8 in
Height: 5-5/8 in



Category: Pendants

Finish: Brushed Bronze (Plated)

Construction: Steel Construction

Glass/Shade: Clear glass Globe

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Prewired	Quantity: One 60 W max. Candelabra Base or LED equivalent	CULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	E12 base Porcelain socket	1-year Limited Warranty
One 6", four 12" lengths of stem included	120 V		
Canopy covers a standard 4" recessed outlet box: 4.75" W., 0.81" ht., 4.75" depth			