

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500285-015 Bonita

Inspired at its roots by an understated beauty and a breathtaking formal elegance, the Bonita Collection Four-Light Polished Chrome Foyer Chandelier will make a stunning addition to any luxurious living space. A magnificent silver cage embraces the drum shades in a teardrop fashion with four chrome arms flowing down from an ornamental circular plate near the top of the design. The shades are held in place by silver candlestick light bases supported by elegantly curved arms.

- Magnificent polished chrome cage embraces the drum shades in teardrop fashion.
- Four polished chrome arms flow down from an ornamental circular plate near the top of the design.
- Polished chrome candlestick light bases supported by elegantly curved arms hold the drum shades in place.
- Ideal for any foyer, entryway, or kitchen.
- Elegant choice for modern, luxury, or transitional interiors.
- Measures 23-inches width by 25-7/8-inch height.
- Uses four candelabra base bulbs that are sold separately (40w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Hall & Foyer

**Finish:** Polished Chrome (Plated)

**Construction:** Steel Construction

**Glass/Shade:** White Linen fabric Shade



Diameter: 23 in  
Height: 25-7/8 in  
Overall Ht. W/Chain: 92 in

White Linen fabric Shade  
Width: 4-1/4 in  
Height: 5-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity:	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	Four 40 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
Six links of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5" W., 0.812" ht., 5" depth			