

Project:		
Fixture Type:		
Location:		
Contact:		

P500285-031

Bonita

Inspired at its roots by an understated beauty and a breathtaking formal elegance, the Bonita Collection Four-Light Black Foyer Chandelier will make a stunning addition to any luxurious living space. A magnificent black cage embraces the drum shades in a teardrop fashion with four stain brass arms flowing down from an ornamental circular plate near the top of the design. The shades are held in place by black candlestick light bases supported by elegantly curved arms.

- · Magnificent black cage embraces the drum shades in teardrop fashion.
- Four black arms flow down from an ornamental circular plate near the top of the design.
- Black candlestick light bases supported by elegantly curved arms hold the drum shades in place.
- · Ideal for any foyer, entryway, or kitchen.
- · Elegant choice for modern, luxury, or transitional interiors.
- Measures 23-inches width by 25-7/8-inch height.
- Uses four candelabra base bulbs that are sold separately (40w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Hall & Foyer Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: White Linen fabric Shade



Diameter: 23 in Height: 25-7/8 in Overall Ht. W/Chain: 92 in

White Linen fabric Shade Width: 4-1/4 in

Width: 4-1/4 in Height: 5-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain mounted	Prewired	Quantity: Four 40 W max. Candelabra Base	CULus Dry Location Listed
	15 feet of wire supplied	or LED equivalent	1-year Limited Warranty
1/8 IP mounting plate for outlet box included	120 V	E12 base Phenolic sockets	
Six links of 9 gauge chain			
supplied			
One 6", four 12" lengths of stem			
included			
Canopy covers a standard 4" recessed outlet box: 5" W., 0.812"			
ht., 5" depth			