

Project:			
Fixture Type:			
Location:			
Contact:			

P500287-020

Brandywine

Whimsical and romantic, this pendant features an interlocking sphere with carefully crafted decorative details. The elegant, antique bronze frame captures a tasteful, timeless look with hand-painted accents. The frame's opencage design is perfect for creating an airy, romanticized glow.

- An interlocking sphere with carefully crafted decorative details manifests a whimsical and romantic pendant.
- The elegant, antique bronze frame captures a tasteful, timeless look with hand-painted accents.
- The frame's open-cage design is perfect for creating an airy, romanticized glow.
- · Ideal for any foyer, kitchen, or dining room.
- Perfect for transitional, new traditional, and farmhouse settings.
- · Measures 22-inch width by 26-inch height.
- Uses five candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Antique Bronze (Painted) **Construction:** Steel Construction



Diameter: 22 in Height: 26 in

Overall Ht. W/Chain: 101 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Five 60 W max. Candelabra Base	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic sockets	
6 feet of 9 gauge chain supplied			
Canopy covers a standard 4" recessed outlet box: 5" W., 1" ht., 5" depth			