

Project:			
Fixture Type:			
Location:			
Contact:			

P500288-009

Classic

You'll absolutely love the angelic demeanor of this mini-pendant. An otherworldly etched glass bell-shaped shade is the focus of this lighting design. The shade hangs from a beautiful brushed nickel light base that is held in place by a delicate stem.

- · Offers any angelic demeanor to any space it inhabits.
- · An etched glass, bell-shaped shade is the focus of this lighting design.
- The shade hangs from a beautiful brushed nickel light base that is held in place by a delicate stem.
- · Ideal for any foyer, kitchen, or dining room.
- · Perfect for transitional settings.
- · Measures 5-1/8-inch width by 7-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Pendants

Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Etched glass bell shaped shade



Diameter: 5-1/8 in Height: 7 in

Overall Ht. W/Chain: 46 in

Etched glass bell shaped shade

Width: 5 in Height: 5-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: One 100 W max. Medium Base or	CULus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	LED equivalent	1-year Limited Warranty
2 feet of 9 gauge chain supplied	120 V	E26 base Porcelain socket	
One 12" length of stem included			
Canopy covers a standard 4"			
recessed outlet box: 5.312" W., 1.06" ht., 5.312" depth			