

Geodesic LED

 Cable Suspension Mounted • Damp Location Listed **PROGRESS LED**

Description:

Geodesic LED Collection Matte Black LED Mid-Century Modern Large Pendant Hanging Light

Specifications:

- Frosted Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5 in W., 1.6 in ht., 5 in depth
- Swivel mounting strap for outlet box included
- 96 in of wire supplied 90 in

Performance:

Number of Modules	1
Input Power	38 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	3,373/88 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2019

P500320-031-30



Dimensions:

Length: 27-1/8 in
 Diameter: 27-1/8 in
 Height: 12-1/4 in
 Overall Ht. W/Cables: 103-3/4 in

Frosted Acrylic Diffuser
 Width: 11-15/16 in
 Height: 0.039 in

P500320-031-30

Dimming Notes:

P500320-031-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Leviton_6674

Lutron_NTEVL-300

Lutron_DVELV-300P

Lutron_Caseta Wireless

Lutron_AYCL-153P

Lutron_SCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.