

### Description:

Kylo LED Collection 1-Light Matte Black Frosted Glass LED Modern Pendant Hanging Light

### Specifications:

- Frosted Acrylic Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W., 4.75 in ht., 1.5 in depth
- Mounting backplate for outlet box included
- 120 in of wire supplied 10 feet

### Performance:

Number of Modules	1
Input Power	6.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	420/64 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed Meets California Title 24 JA8-2019

# P500321-031-30



### Dimensions:

Length: 4-3/4 in  
 Diameter: 4-3/4 in  
 Height: 13 in  
 Overall Ht. W/Cables: 132-5/8 in

Frosted Acrylic Cylindrical  
 Width: 1-1/4 in  
 Height: 7 in

# P500321-031-30

## Dimming Notes:

---

P500321-031-30 is designed to be compatible with many ELV controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.