

Project:
Fixture Type:
Location:

Kylo LED

Cable Suspension Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

Kylo LED Collection 6-Light Brushed Nickel Frosted Glass LED Modern Pendant Hanging Light

Specifications:

- · Frosted Acrylic Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 11.75 in W., 11.75 in ht., 1.5 in depth
- · Mounting backplate for outlet box included
- 120 in of wire supplied 10 feet

Performance:

Number of Modules	6
Input Power	24 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,790/77 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2019

P500322-009-30



Dimensions:

Length: 11-3/4 in Height: 13 in

Overall Ht. W/Cables: 132-5/8 in

Frosted Acrylic Cylindrical

Width: 1-1/4 in Height: 7 in



Kylo LED

Cable Suspension Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P500322-009-30

P500322-009-30 is designed to be compatible with many ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.