

Project:

Fixture Type:

Location:

Contact:

P500325-104 Hinton

Hinton Collection 1-Light Polished Nickel Vintage Pendant Hanging Light

Category: Pendants

Finish: Polished Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Polished Nickel Steel Cone



Length: 12-1/4 in Diameter: 12-1/4 in Height: 12-3/4 in

Overall Ht. W/Chain Or Stem: 78-1/2 in

Polished Nickel Steel Cone

Width: 12-1/4 in Height: 8-7/8 in

	Height: 8-//8 in			
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Ceiling Stem Hung with 6 links of chain Mounting plate for outlet box included six links of 9 gauge chain supplied one 6", four 12" lengths of stem included Canopy covers a standard 4" recessed outlet box: 4.87" W., 4.87" ht., 0.75" depth	10 feet of wire supplied 120 V	Quantity: one 100 W max. E26 base Porcelain Socket	cULus Dry Location Listed 1-year Limited Warranty	