

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500344-185 Chastain

Chastain Collection Three-Light Bleached Oak Basket Farmhouse Pendant Light

Category: Pendants
Finish: Bleached Oak (Hand Painted)
Construction: Steel Construction
Glass/Shade: Bleached Oak Metal



Diameter: 20-7/8 in
Height: 25-1/4 in
Overall Ht. W/Stem: 91-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted with 6 links of chain/stem or semi-flush mount directly to canopy	15 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Six links of 9 Gauge gauge chain supplied (1)		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			