

Project:

Fixture Type:

Location:

Contact:

P500355-030 5IN CYL RNDS

Cylinder Collection 5-Inch 1-Light White Modern Outdoor Pendant Hanging Light

Category: Cylinder Finish: White (Painted)

Construction: Aluminum Housing



Length: 5 in Diameter: 5 in Height: 9.8 in

Height: 9.8 in

Overall Ht. W/Cord: 130-1/29 in

	Overall Ht. W/Cord: 130-1/29 in		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	Quantity: one 65 W max. PAR30 or LED	cCSAus Damp Location Listed
Mounting strap for outlet box included	120 VAC	equivalent	1-year Limited Warranty
		E26 base Socket	
Canopy covers a standard 4" recessed outlet box: 4.72" W., 0.79" ht., 4.72" depth			