

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

## P500357-009 Saffert

Saffert Collection Three-Light New Traditional Brushed Nickel White Linen Shade Pendant Light

**Category:** Pendants  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** White Linen Fabric Shade (Tapered), Diffuser Glass Disc



Diameter: 22 in  
 Height: 30 in  
 Overall Ht. W/Chain: 105 in

White Linen Fabric Shade (Tapered)  
 Width: 20-7/8 in  
 Height: 9-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.812" ht., 5" depth		Fully dimmable with dimmable bulbs	