



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500358-009 Delayne

Delayne Collection One-Light Mid-Century Modern Brushed Nickel Etched Opal Glass Pendant Light

Category: Pendants
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Globe



Diameter: 9-3/8 in
 Height: 12-3/8 in
 Overall Ht. W/Chain Or Stem: 72-1/2 in

Etched Opal Glass Globe
 Width: 8 in
 Height: 7-5/16 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|--------------------------|--|---------------------------|
| Ceiling Chain | 10 feet of wire supplied | (1) Medium Base (E26) Socket | cULus Dry Location Listed |
| Mounting plate for outlet box included | 120 VAC | Lamp Type A19 | 1-year Limited Warranty |
| 6 links of 9 Gauge chain supplied with quick link | | Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket | |
| One 6", four 12" lengths of stem included | | Fully dimmable with dimmable bulbs | |
| Canopy covers a standard 4" recessed outlet box: 5.18" W., 0.81" ht., 5.18" depth | | | |