

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500360-109 Parkhurst

Parkhurst Collection One-Light New Traditional Brushed Bronze Clear Glass Mini-Pendant Light

Category: Pendants

Finish: Brushed Bronze (Plated)

Construction: Steel Construction

Glass/Shade: Clear Glass Bell



Diameter: 11-1/2 in
Height: 16-3/4 in
Overall Ht. W/Chain Or Stem: 83 in

Clear Glass Bell
Width: 9-7/16 in
Height: 9-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.68" W., 1" ht., 5.68" depth			