

Project:			
Fixture Type:			
Location:			
Contact:			

P500360-31M

Parkhurst

Parkhurst Collection One-Light New Traditional Matte Black Clear Glass Mini-Pendant Light

Category: Pendants

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell



Diameter: 11-1/2 in Height: 16-3/4 in

Overall Ht. W/Chain Or Stem: 83 in

Clear Glass Bell Width: 9-7/16 in Height: 9-13/16 in

	0 3 31				
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION		
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed		
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty		
6 links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket			
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs			
Canopy covers a standard 4" recessed outlet box: 5.68" W., 1" ht., 5.68" depth					