

Project:

Fixture Type:

Location:

Contact:

P500361-109

Parkhurst

Parkhurst Collection One-Light New Traditional Brushed Bronze Clear Glass Pendant Light

Category: Pendants

Finish: Brushed Bronze (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl



Diameter: 15-1/4 in Height: 23-3/8 in

Overall Ht. W/Chain Or Stem: 89-1/2 in

Clear Glass Bowl Width: 13-3/8 in Height: 14 in

		9 1	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.68" W., 1" ht., 5.68" depth			