



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500363-009

Elara

Elara Collection Four-Light New Traditional Brushed Nickel Chandelier Foyer Light

Category: Hall & Foyer
Finish: Brushed Nickel (Plated)
Construction: Steel Construction



Diameter: 15 in
Height: 31-3/8 in
Overall Ht. W/Stem: 88-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.75" W., 1" ht., 5.75" depth		Fully dimmable with dimmable bulbs	