

Project:

Fixture Type:

Location:

Contact:

## P500365-028

## Lorin

Lorin Collection One-Light Mid-Century Modern Satin White Metal Pendant Light

Category: Pendants

Finish: Satin White (Painted) with Brushed Bronze accent

**Construction:** Steel Construction

Glass/Shade: Satin White Metal Flared Cone



Diameter: 18 in Height: 16 in

Overall Ht. W/Cord: 127 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		LED: 12.5-watt MAX per socket	
•		Fully dimmable with dimmable bulbs	