

Project:
Fixture Type:
Location:

## **Everlume LED**

Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

Contact:

### **Description:**

Everlume LED Collection Modern Brushed Nickel Pendant


### **Specifications:**

- · Brushed Nickel Metal Frame
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.5 in W., 2 in ht., 5.5 in depth
- · Mounting strap for outlet box included
- 120 in of wire supplied

### **Performance:**

Number of Lights	1
Input Power	20 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,697/84 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2019

# P500366-009-30



#### **Dimensions:**

Diameter: 11 in Height: 2-1/4 in

Overall Ht. W/Cord: 122 in



### **Everlume LED**

Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

### **Dimming Notes:**

P500366-009-30

 $\ensuremath{\mathsf{P500366\text{-}009\text{-}30}}$  is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls:**

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.