

Project:		
Fixture Type:		
Location:		
Contact:		

## P500367-009

## **Parkhurst**

Parkhurst Collection One-Light New Traditional Brushed Nickel Metal Pendant Light

Category: Pendants

**Finish:** Brushed Nickel (Plated) **Construction:** Steel Construction

Glass/Shade: Brushed Nickel Metal Dome



Diameter: 12-3/8 in Height: 11-7/8 in Overall Ht. W/Stem: 68 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Ceiling Stem	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed	
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty	
One 6", four 12" lengths of stem included	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth	Fully dimmable with dimmable bulbs			