

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500368-009 Parkhurst

Parkhurst Collection Three-Light New Traditional Brushed Nickel Metal Pendant Light

Category: Pendants

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Brushed Nickel Metal Dome



Diameter: 17-7/8 in
Height: 15-1/4 in
Overall Ht. W/Stem: 72 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1" ht., 5.12" depth		Fully dimmable with dimmable bulbs	