

Inverse LED

Ceiling Chain Mounted • Damp Location Listed **PROGRESS LED**

Description:

Inverse LED Collection Modern Brushed Nickel Pendant

Specifications:

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6 in W., 1.5 in ht., 6 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied 96 in

Performance:

| | |
|------------------------|---|
| Number of Modules | 1 |
| Input Power | 27 W |
| Input Voltage | 120 V |
| Input Frequency | 60 Hz |
| Lumens/LPW (Delivered) | 1,641/60 (LM-79) |
| CCT | 3000 K |
| CRI | 90 CRI |
| Life (hours) | 50000 (L70/TM-21) |
| EMI/RFI | FCC Title 47, Part 15, Class B |
| Warranty | 5-year Limited Warranty |
| Labels | cCSAus Damp Location Listed Meets California Title 24 JA8-2019 |

P500369-009-30



Dimensions:

Diameter: 20 in
Height: 2-3/8 in
Overall Ht. W/Cables: 100 in

White Polycarbonate Diffuser

P500369-009-30

Dimming Notes:

P500369-009-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.