

## Inverse LED

Ceiling Chain Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Inverse LED Collection Modern Matte Black Pendant

### Specifications:

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6 in W., 1.5 in ht., 6 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied 96 in

### Performance:

Number of Modules	1
Input Power	27 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,641/60 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2019

# P500369-31M-30



### Dimensions:

Length: 20 in  
Diameter: 20 in  
Height: 2-3/8 in  
Overall Ht. W/Cables: 100 in

White Polycarbonate Diffuser

# P500369-31M-30

**Dimming Notes:**

---

P500369-31M-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls:**

---

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.