

Project:

Fixture Type:

Location:

Contact:

Inverse LED

Ceiling Chain Mounted · Damp Location Listed PROGRESS LED

Description: D5

Inverse LED Collection Modern Matte Black Pendant

Specifications:

- · White Polycarbonate Diffuser
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6 in W., 1.5 in ht., 6 in depth
- · Mounting strap for outlet box included
- 6 in of wire supplied 96 in

Performance:

| 1 |
|------------------------------------|
| 35 W |
| 120 V |
| 60 Hz |
| 2,364/62 (LM-79) |
| 3000 K |
| 90 CRI |
| 50000 (L70/TM-21) |
| FCC Title 47, Part 15, Class B |
| 5-year Limited Warranty |
| cCSAus Damp Location Listed |
| Meets California Title 24 JA8-2019 |
| |

P500370-31M-30



Dimensions:

Diameter: 30 in Height: 2-3/8 in

Overall Ht. W/Cables: 100 in

White Polycarbonate Diffuser



Inverse LED

Ceiling Chain Mounted • Damp Location Listed PROGRESS LED

P500370-31M-30

Dimming Notes:

 $\ensuremath{\mathsf{P500370\text{-}31M\text{-}30}}$ is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.