

Project:			
Fixture Type:			
Location:			
Contost			

P500371-009

Parkhurst

Parkhurst Collection Eight-Light New Traditional Brushed Nickel Chandelier Foyer Light

Category: Hall & Foyer Finish: Brushed Nickel (Plated) Construction: Steel Construction



Square: 20 in Height: 36 in

Overall Ht. W/Chain: 108 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(8) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
6 feet of 9 Gauge chain supplied		socket	
with quick link		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.68" W., 1" ht., 5.68" depth		Fully dimmable with dimmable bulbs	