

Project:
Fixture Type:
Location:

## Radian LED

Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

Contact:

### **Description:**

Radian LED Collection Modern Satin White Metal Pendant

### **Specifications:**

- · Satin White Metal Dome
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 5 in W., 1.5 in ht., 5 in depth
- Mounting strap for outlet box included
- 120 in of wire supplied

#### **Performance:**

Number of Lights	1
Input Power	20 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	990/49 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2019

# P500372-028-30



### **Dimensions:**

Diameter: 10-1/2 in Height: 10 in

Overall Ht. W/Cord: 131 in



## Radian LED

Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

### **Dimming Notes:**

P500372-028-30

 $\ensuremath{\mathsf{P500372\text{-}}028\text{-}30}$  is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls:**

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.