

Project:

Fixture Type:

Tixture

Location: Contact:

Radian LED

Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

Description:

Radian LED Collection Modern Brushed Nickel Metal Pendant

Specifications:

- Brushed Nickel Metal Dome
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5 in W., 1.5 in ht., 5 in depth
- $\boldsymbol{\cdot}$ Mounting strap for outlet box included
- + 120 in of wire supplied

Performance:

Number of Lights	1
Input Power	30 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,546/51 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2019

P500373-009-30



Dimensions:

Diameter: 16 in Height: 14 in Overall Ht. W/Cord: 133 in



Radian LED

Ceiling Cord Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

 $\mathsf{P500373}\text{-}009\text{-}30$ is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTEVL-300

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P500373-009-30