

Project:			
Fixture Type:			
Location:			
Contact			

P500378-009 **Galloway**

Category: Hall & Foyer

Finish: Brushed Nickel (Plated) with Grey Washed Oak accent

Construction: Steel Construction



Diameter: 24 in

Height: 30-7/8 in Overall Ht. W/Chain: 106-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
6 feet of 9 Gauge chain supplied		socket	
with quick link		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	