PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:



Perimeter Collection One-Light Brushed Nickel Mid-Century Modern Pendant with metal Shade

Category: Pendants Finish: Brushed Nickel (Plated) with Painted White Interior accent Construction: Steel Construction Glass/Shade: Brushed Nickel Metal Dome



Diameter: 15-3/4 in Height: 8-5/8 in Overall Ht. W/Cord: 120-1/2 in

Brushed Nickel Metal Dome Width: 15-3/4 in Height: 7-15/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	