

Project:		
Fixture Type:		
Location:		
Contact:		

## P500380-191

## **Perimeter**

Perimeter Collection One-Light Brushed Gold Mid-Century Modern Pendant with metal Shade

Category: Pendants

Finish: Brushed Gold (Plated) with Painted White Interior accent

**Construction:** Steel Construction

Glass/Shade: Brushed Gold Metal Dome



Diameter: 23-5/8 in Height: 12-1/2 in

Overall Ht. W/Cord: 124-1/2 in

Brushed Gold Metal Dome

Width: 23-5/8 in Height: 11-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19 Incandescent: 100-watt MAX per	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth		socket LED: 17.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	