

Project:		
Fixture Type:		
Location:		
Contact:		

P500380-31M

Perimeter

Perimeter Collection One-Light Matte Black Mid-Century Modern Pendant with metal Shade

Category: Pendants

Finish: Matte Black (Painted) with Painted White Interior accent

Construction: Steel Construction **Glass/Shade:** Matte Black Metal Dome



Diameter: 23-5/8 in Height: 12-1/2 in

Overall Ht. W/Cord: 124-1/2 in

Matte Black Metal Dome Width: 23-5/8 in Height: 11-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.87" W., 0.87" ht., 4.87" depth		LED: 17.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	