

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500381-009 Singleton

Category: Pendants
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl



Diameter: 14 in
Height: 8-1/2 in
Overall Ht. W/Stem: 65 in

Clear Glass Bowl
Width: 14 in
Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with Swivel	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem included plus 90-deg swivel for installation on sloped ceilings		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		Fully dimmable with dimmable bulbs	