

Project:

Fixture Type:

Location:

Contact:

P500382-163

Hinton

Hinton Collection One-Light Brushed Nickel Modern Farmhouse Pendant

Category: Pendants

Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Seeded Glass Cone



Diameter: 8 in Height: 8-5/8 in

Overall Ht. W/Cord: 118 in

Clear Seeded Glass Cone

Width: 8 in Height: 5-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	