

Project:

Fixture Type:

Location:

Contact:

## P500383-163

## **Hinton**

Hinton Collection One-Light Vintage Brass Modern Farmhouse Pendant

Category: Pendants

Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Vintage Brass Metal Cone



Diameter: 8-1/4 in Height: 8-5/8 in

Overall Ht. W/Cord: 118 in

Vintage Brass Metal Cone Width: 8 in

Width: 8 in Height: 5-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		LED: 12.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	