

Project:

Fixture Type:

Location:

Contact:

## P500383-31M

## **Hinton**

Hinton Collection One-Light Matte Black Modern Farmhouse Pendant

Category: Pendants

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Matte Black Metal Cone



Diameter: 8-1/4 in Height: 8-5/8 in

Overall Ht. W/Cord: 118 in

Matte Black Metal Cone

Width: 8 in Height: 5-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		LED: 12.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	