

Project:

Fixture Type:

Location:

Contact:

P500384-31M

Hinton

Hinton Collection One-Light Matte Black Modern Farmhouse Pendant

Category: Pendants
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Seeded Glass Cone



Diameter: 16 in Height: 14 in

Overall Ht. W/Stem and 6 links of chain: 79 in

Clear Seeded Glass Cone

Width: 16 in Height: 10-1/2 in

		g ,	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
Mounting plate for outlet box included		Incandescent: 100-watt MAX per	,
Six links of 9 Gauge chain supplied		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable	
One 6", four 12" lengths of stem included		bulbs	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth			