

Project:

Fixture Type:

Location:

Contact:

P500386-194

Markor

Markor Collection One-Light Ecru Linen Shade Transitional Pendant

Category: Pendants

Finish: Brushed Nickel, Matte Black, Vintage Brass (Painted)

Construction: Steel Construction

Glass/Shade: Ecru Linen Fabric Cylindrical, Sand Blast Acrylic Flat Round

Diffuser



Diameter: 12 in Height: 10 in

Overall Ht. W/Cord: 122 in

Ecru Linen Fabric Cylindrical

Width: 12 in Height: 10 in

Sand Blast Acrylic Flat Round Diffuser

Width: 12 in Height: 0-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		LED: 17.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	