## PROGRESS LIGHTING<sup>\*\*</sup>

Project:

Fixture Type:

Location:

\_

Contact:



## P500387-194 Markor

Markor Collection One-Light Ecru Linen Shade Transitional Pendant

Category: Pendants Finish: Brushed Nickel, Matte Black, Vintage Brass (Painted) Construction: Steel Construction Glass/Shade: Ecru Linen Fabric Cylindrical, Sand Blast Acrylic Flat Round Diffuser



Diameter: 18-1/8 in Height: 10 in Overall Ht. W/Cord: 122 in

Ecru Linen Fabric Cylindrical Width: 18-1/4 in Height: 10 in

Sand Blast Acrylic Flat Round Diffuser Width: 18 in Height: 0-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19 Incandescent: 60-watt MAX per	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		socket LED: 12.5-watt MAX per socket	
,,		Fully dimmable with dimmable bulbs	