

Project:

Fixture Type:

Location:

Contact:

P500390-009 Gilliam

Gilliam Collection Three-Light Brushed Nickel New Traditional Hall & Foyer

Category: Hall & Foyer Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Curved Panel



Diameter: 10 in Height: 20-3/4 in

Overall Ht. W/Chain: 84 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	96 in of wire supplied	(3) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
E fact of O Course above available		Incandescent: 60-watt MAX per	
5 feet of 9 Gauge chain supplied with quick link		socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	