

Project:		
Fixture Type:		
Location:		
Contact:		

P500390-31M Gilliam

Gilliam Collection Three-Light Matte Black New Traditional Hall & Foyer

Category: Hall & Foyer Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Curved Panel



Diameter: 10 in Height: 20-3/4 in

Overall Ht. W/Chain: 84 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	96 in of wire supplied	(3) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	