

Project:

Fixture Type:

Location:

Contact:

P500391-163

Gilliam

Gilliam Collection Four-Light Vintage Brass New Traditional Hall & Foyer

Category: Hall & Foyer Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Curved Panel



Diameter: 15 in Height: 30-5/8 in

Overall Ht. W/Chain: 93-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	96 in of wire supplied	(4) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
5 feet of 9 Gauge chain supplied		socket	
with quick link		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable	
recessed outlet box: 5.12" W.,		bulbs	
0.75" ht., 5.12" depth			