PROGRESS LIGHTING DESIGN**+SERIES**™

Project:	 	
Fixture Type:		
Location:		
Contact:		



0.81" ht., 5.12" depth

Trimble Collection One-Light Brushed Nickel Mini Pendant

Category: Pendants Finish: Brushed Nickel (Plated) with Graphite accent Construction: Steel Construction



Diameter: 8 in Height: 2.5 in (does not include bulb) Overall Ht. W/Stem And Swivel: 59 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
1/8 IP mounting plate for outlet box included		Incandescent: 60-watt MAX per socket	
with quick link		LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.12" W.,			